

# A-Z ORTO

LABORATORIUM

ORTODONTYCZNE

ELIZA GŁOWACKA

## ZAMKI SAMOLIGATURUJACE


ZAMKI KOREA – SZWECJA


METAL

KLAPKA Z NiTi


022 I 018

1 szt . 24,00







**Passive Phase**  
Small round wires slide freely, initiating the tooth movement process as the archwire gently levels the teeth and coaxes them into alignment.



**Expressive Phase**  
Square or rectangular wires are seated into the base of the slot without contacting the clip. Rotations are corrected and space closures are completed.



**Active Phase**  
Rectangular archwires extend beyond the slot to fully engage the clip, providing the active control necessary for finishing uprighting of the roots and adjusting the torque




ROTH lub MBT

SLB Damon III Prescription

SLB Damon I Prescription

Position	Torque(°)	Angulation(°)
Upper Central	+2	+5
Upper Lateral	-5	+9
Upper Cuspid	+7	+5
Upper Bicuspid	-11	+2
Lower Central	-11	+2
Lower Lateral	-11	+4
Lower Cuspid	+7	+5
Lower 1st Bicuspid	-12	+4
Lower 2nd Bicuspid	-17	+4

Position	Torque(°)	Angulation(°)
Upper Central	+15	+5
Upper Lateral	+6	+9
Upper Cuspid	+7	+5
Upper Bicuspid	-11	+2
Lower Central	-3	+2
Lower Lateral	-3	+4
Lower Cuspid	+7	+5
Lower 1st Bicuspid	-12	+4
Lower 2nd Bicuspid	-17	+4

SLB Damon II Prescription

Position	Torque(°)	Angulation(°)
Upper Central	+22	+5
Upper Lateral	+13	+9
Upper Cuspid	+11	+5
Upper Bicuspid	-11	+2
Lower Central	-3	+2
Lower Lateral	-3	+4
Lower Cuspid	+13	+5
Lower 1st Bicuspid	-5	+4
Lower 2nd Bicuspid	-17	+4

1 szt 24,00





## CERAMIKA , KLAPKA NITI

ROTH LUB MBT 1 szt 24,90



## CAŁE ESTETYCZNE - KLAPKA TEZ

CENA 1 szt 32,00

THOMAS C



**Cabriolet** the clear hybrid self-ligating ortho appliance  
ROTH LUB MBT

- 1 Polymer snap-on door for easy and fast closing/ opening - also protects in trauma situations.
- 2 Ceramic body for strength and secure bonding. – slim design with low profile.
- 3 Centred T hook for elastics and fits all NiTi chains.
- 4 Both passive and active.
- 5 Stainless steel hinge.
- 6 Metal insert for reduced wire- friction.
- 7 Radius in base for easier de-bonding.
- 8 FDI notation in base for easy identification

